





Artikel	E-Nummer	Håltagning:	Dimensioner:	Beskrivning:	
MST 2	79 900 22	75 - 90 - 110 - 127 mm.	Dia, 200 mm.		
MST 5	79 900 25	67 - 80 - 100 mm.	Dia, 190 mm.		
MST 12		130 mm.	Dia, 200 mm.		
MST 44		74 x 72 mm.			
MST 56		38 mm.	Dia, 200 mm.		
MST 60	73 487 29	100 mm.	Dia, 290 mm.		
MST 62		100 mm.	Dia, 175 mm.		
MST 93		92 mm.	Dia, 180 mm.		
MST 94		111 mm.	Dia, 200 mm.		
MST 96		105 mm.	Dia, 170 mm.		
MST 105		63 mm.	Dia, 180 mm.		
MST 150		84 mm.	Dia, 125 mm.		
MST 170		112 mm.	Dia, 140 mm.		
MST 196		87 mm.	Dia, 180 mm.		
MST 1	79 900 21	190 - 205 - 225 mm.	595 x 360 x 2,8 mm.		
MST 3	79 900 23	200 - 222 - 254 mm.	595 x 360 x 2,8 mm.		
MST 4	79 900 24	130 - 155 - 170 mm.	595 x 360 x 2,8 mm.		
MST 14		175 mm.	595 x 360 x 2,8 mm.		
MST 17		125 mm.	595 x 360 x 2,8 mm.		
MST 18		207 mm.	595 x 360 x 2,8 mm.		
MST 19		235 mm.	595 x 360 x 2,8 mm.		
MST 20		217 mm.	595 x 360 x 2,8 mm.		
MST 21		241 mm.	595 x 360 x 2,8 mm.		
MST 24		244 mm.	595 x 360 x 2,8 mm.		
MST 41		245 mm.	595 x 360 x 2,8 mm.		
MST 43		185 mm.	595 x 360 x 2,8 mm.		
MST 45		145 mm.	595 x 360 x 2,8 mm.		
MST 49		195 mm.	595 x 360 x 2,8 mm.		
MST 51		180 mm.	595 x 360 x 2,8 mm.		
MST 52		171 mm.	595 x 360 x 2,8 mm.		
MST 53		215 mm.	595 x 360 x 2,8 mm.		
MST 58		165 mm.	595 x 360 x 2,8 mm.		
MST 61		260 mm.	595 x 360 x 2,8 mm.		
MST 68		200 mm.	595 x 360 x 2,8 mm.		
MST 70		115 mm.	595 x 360 x 2,8 mm.		
MST 73		400 mm.	595 x 360 x 2,8 mm.		
MST 74		300 mm.	595 x 360 x 2,8 mm.		
MST 78		160 mm.	595 x 360 x 2,8 mm.		
MST 80		90 mm.	595 x 360 x 2,8 mm.		
MST 83		155 mm.	595 x 360 x 2,8 mm.		
MST 86		225 mm.	595 x 360 x 2,8 mm.		
MST 87		220 mm.	595 x 360 x 2,8 mm.		
MST 90		180 mm x 2 (240 mm CC).	595 x 360 x 2,8 mm.		
MST 91		290 mm.	595 x 360 x 2,8 mm.		
MST 97		255 mm.	595 x 360 x 2,8 mm.		




Senast uppdaterad: 2011-06-03

Kontaktperson: Martin Amnehag
Tele/orderfax: +46 303 888 89
Mobil: +46 708 278 373

Artikel	E-Nummer	Håltagning:	Dimensioner:	Beskrivning:
MST 99		170 mm.	595 x 360 x 2,8 mm.	Sid. 1
MST 106		516 mm.	595 x 595 x 2,8 mm.	
MST 108		314 mm.	595 x 360 x 2,8 mm.	
MST 115		516 mm.	595 x 360 x 2,8 mm.	
MST 116		110 mm.	595 x 360 x 2,8 mm.	
MST 117		205 mm.	595 x 360 x 2,8 mm.	
MST 118		Bokad	595 x 360 x 2,8 mm.	
MST 119		Bokad	595 x 360 x 2,8 mm.	
MST 121		186 mm.	595 x 360 x 2,8 mm.	
MST 122		275 mm.	595 x 360 x 2,8 mm.	
MST 123		272 mm.	595 x 360 x 2,8 mm.	
MST 125		100 mm.	595 x 360 x 2,8 mm.	
MST 128		280 mm.	595 x 360 x 2,8 mm.	
MST 135		156 mm.	595 x 360 x 2,8 mm.	
MST 138		360 mm.	595 x 400 x 2,8 mm.	
MST 139		195 x 2 (256 CC) mm.	595 x 360 x 2,8 mm.	
MST 151		547 mm.	595 x 595 x 2,8 mm.	
MST 152		130 mm.	595 x 360 x 2,8 mm.	
MST 153		134 mm.	595 x 360 x 2,8 mm.	
MST 154		80 mm.	595 x 360 x 2,8 mm.	
MST 155		305 mm.	595 x 360 x 2,8 mm.	
MST 157		140 mm.	595 x 360 x 2,8 mm.	
MST 166		128 mm.	595 x 360 x 2,8 mm.	
MST 184		208 mm.	595 x 360 x 2,8 mm.	
MST 186		108 mm.	595 x 360 x 2,8 mm.	
MST 193		120 mm.	595 x 360 x 2,8 mm.	
MST 194		104 mm.	595 x 360 x 2,8 mm.	
MST 195		146 mm.	595 x 360 x 2,8 mm.	
MST 201		190 mm.	595 x 360 x 2,8 mm.	
MST 202		198 mm.	595 x 360 x 2,8 mm.	
MST 203		210 mm.	595 x 360 x 2,8 mm.	
MST 205		267 mm.	595 x 360 x 2,8 mm.	
MST 206		114 mm.	595 x 360 x 2,8 mm.	
MST 207		230 mm.	595 x 360 x 2,8 mm.	
MST 208		150 mm.	595 x 360 x 2,8 mm.	
MST 216		117 mm.	595 x 360 x 2,8 mm.	
MST 302		360 mm.	595 x 420 x 2,8 mm.	

Artikel	E-Nummer	Håltagning:	Dimensioner:	Beskrivning:
MST 22		170 x 170 mm.	595 x 360 x 2,8 mm.	
MST 23		349 x 170 mm.	595 x 360 x 2,8 mm.	
MST 26		135 x 190 mm.	595 x 360 x 2,8 mm.	
MST 30		358 x 128 mm.	595 x 360 x 2,8 mm.	
MST 32		385 x 128 mm.	595 x 360 x 2,8 mm.	
MST 34		180 x 460 mm x 2 ,radie 90.	595 x 595 x 2,8 mm.	
MST 35		210 x 162 mm.	595 x 360 x 2,8 mm.	
MST 47		247 x 137 mm.	595 x 360 x 2,8 mm.	
MST 48		135 x 215 mm.	595 x 360 x 2,8 mm.	
MST 50		193 x 129 mm.	595 x 360 x 2,8 mm.	
MST 59		185 x 185 mm.	595 x 360 x 2,8 mm.	
MST 63		530 x 180 mm.	595 x 360 x 2,8 mm.	
MST 64		180 x 180 mm.	595 x 360 x 2,8 mm.	
MST 65		350 x 180 mm.	595 x 360 x 2,8 mm.	
MST 66		350 x 350 mm.	595 x 360 x 2,8 mm.	
MST 67		205 x 205 mm.	595 x 360 x 2,8 mm.	
MST 69		220 x 130 mm.	595 x 360 x 2,8 mm.	
MST 71		355 x 162 mm.	595 x 360 x 2,8 mm.	
MST 72		261 x 200 mm.	595 x 360 x 2,8 mm.	
MST 75		405 x 42 mm.	595 x 360 x 2,8 mm.	
MST 76		310 x 160 mm.	595 x 360 x 2,8 mm.	
MST 77		385 x 385 mm.	595 x 360 x 2,8 mm.	
MST 79		490 x 180 mm.	595 x 360 x 2,8 mm.	
MST 82		163 x 163 mm.	595 x 360 x 2,8 mm.	
MST 84		272 x 48 mm.	595 x 360 x 2,8 mm.	
MST 85		490 x 170 mm.	595 x 360 x 2,8 mm.	
MST 88		253 x 253 mm.	595 x 360 x 2,8 mm.	
MST 92		400 x 374 mm.	595 x 360 x 2,8 mm.	
MST 98		490 x 161 mm.	595 x 360 x 2,8 mm.	
MST 92		400 x 374 mm.	595 x 360 x 2,8 mm.	
MST 98		490 x 161 mm.	595 x 360 x 2,8 mm.	
MST 100		240 x 192 mm.	595 x 360 x 2,8 mm.	
MST 104		390 x 192 mm.	595 x 360 x 2,8 mm.	
MST 107		210 x 125 mm.	595 x 360 x 2,8 mm.	
MST 110		208 x 208 mm.	595 x 360 x 2,8 mm.	
MST 111		187 x 187 mm.	595 x 360 x 2,8 mm.	
MST 124		310 x 310 mm.	595 x 360 x 2,8 mm.	
MST 126		95 x 95 mm.	595 x 360 x 2,8 mm.	
MST 127		190 x 95 mm.	595 x 360 x 2,8 mm.	
MST 129		210 x 210 mm.	595 x 360 x 2,8 mm.	
MST 130		295 x 295 mm.	595 x 360 x 2,8 mm.	
MST 131		145 x 72 mm.	595 x 360 x 2,8 mm.	
MST 132		298 x 155 mm.	595 x 360 x 2,8 mm.	
MST 133		110 x 110 mm.	595 x 360 x 2,8 mm.	
MST 134		220 x 110 mm.	595 x 360 x 2,8 mm.	



Artikel	E-Nummer	Håltagning:	Dimensioner:	Beskrivning:
MST 136		155 x 155 mm.	595 x 360 x 2,8 mm.	
MST 137		150 x 125 mm.	595 x 360 x 2,8 mm.	
MST 140		163 x 153 mm.	595 x 360 x 2,8 mm.	
MST 141		277 x 153 mm.	595 x 360 x 2,8 mm.	
MST 142		330 x 170 mm.	595 x 360 x 2,8 mm.	
MST 143		215 x 215 mm.	595 x 360 x 2,8 mm.	
MST 144		125 x 125 mm.	595 x 360 x 2,8 mm.	
MST 146		150 x 145 mm.	595 x 360 x 2,8 mm.	
MST 147		285 x 150 mm.	595 x 360 x 2,8 mm.	
MST 148		300 x 120 mm.	595 x 360 x 2,8 mm.	
MST 149		333 x 185 mm.	595 x 360 x 2,8 mm.	
MST 156		148 x 148 mm.	595 x 360 x 2,8 mm.	
MST 158		115 x 115 mm.	595 x 360 x 2,8 mm.	
MST 159		240 x 115 mm.	595 x 360 x 2,8 mm.	
MST 160		360 x 115 mm.	595 x 360 x 2,8 mm.	
MST 161		400 x 200 mm.	595 x 360 x 2,8 mm.	
MST 162		183 x 88 mm.	595 x 360 x 2,8 mm.	
MST 163		72 x 66 mm.	595 x 360 x 2,8 mm.	
MST 164		118 x 72 mm.	595 x 360 x 2,8 mm.	
MST 165		340 x 187 mm.	595 x 360 x 2,8 mm.	
MST 167		150 x 150 mm.	595 x 360 x 2,8 mm.	
MST 168		415 x 150 mm.	595 x 360 x 2,8 mm.	
MST 169		281 x 152 mm.	595 x 360 x 2,8 mm.	
MST 171		163 x 155 mm.	595 x 360 x 2,8 mm.	
MST 172		322 x 155 mm.	595 x 360 x 2,8 mm.	
MST 173		487 x 155 mm.	595 x 360 x 2,8 mm.	
MST 174		100 x 75 mm.	595 x 360 x 2,8 mm.	
MST 175		180 x 75 mm.	595 x 360 x 2,8 mm.	
MST 176		265 x 75 mm.	595 x 360 x 2,8 mm.	
MST 180		172 x 172 mm.	595 x 360 x 2,8 mm.	
MST 181		364 x 172 mm.	595 x 360 x 2,8 mm.	
MST 182		556 x 172 mm.	595 x 360 x 2,8 mm.	
MST 183		364 x 364 mm.	595 x 360 x 2,8 mm.	
MST 187		495 x 155 mm.	595 x 360 x 2,8 mm.	
MST 188		160 x 85 mm.	595 x 180 x 2,8 mm.	
MST 189		325 x 55 mm.	595 x 120 x 2,8 mm.	
MST 190		195 x 2 mm (256 CC).	595 x 360 x 2,8 mm.	
MST 191		222 x 128 mm.	595 x 360 x 2,8 mm.	
MST 192		155 x 83 mm.	595 x 360 x 2,8 mm.	
MST 197		355 x 166 mm.	595 x 360 x 2,8 mm.	
MST 198		420 x 215 mm.	595 x 360 x 2,8 mm.	
MST 199		295 x 150 mm.	595 x 360 x 2,8 mm.	
MST 200		245 x 245 mm.	595 x 360 x 2,8 mm.	
MST 204		323 x 175 mm.	595 x 360 x 2,8 mm.	
MST 209		163 x 153 mm.	595 x 360 x 2,8 mm.	



Senast uppdaterad: 2011-06-03

Kontaktperson: Martin Amnehag
Tele/orderfax: +46 303 888 89
Mobil: +46 708 278 373

Artikel	E-Nummer	Håltagning:	Dimensioner:	Beskrivning:
MST 211		570 x 255 mm.	595 x 360 x 2,8 mm.	A technical drawing showing a square hole centered within a larger rectangular frame, representing the cross-section of a hole in a plate.
MST 212		340 x 180 mm.	595 x 360 x 2,8 mm.	
MST 213		370 x 120 mm.	595 x 360 x 2,8 mm.	
MST 214		315 x 166 mm.	595 x 360 x 2,8 mm.	
MST 215		310 x 160 mm.	595 x 360 x 2,8 mm.	
MST 217		392 x 153 mm.	595 x 360 x 2,8 mm.	
MST 218		425 x 215 mm.	595 x 360 x 2,8 mm.	
MST 219		210 x 165 mm.	595 x 360 x 2,8 mm.	
MST 220		400 x 90 mm.	595 x 360 x 2,8 mm.	
MST 301		330 x 157 mm.	595 x 360 x 2,8 mm.	
MST 303		355 x 142 mm.	595 x 360 x 2,8 mm.	

Artikel	E-Nummer	Håltagning:	Dimensioner:	Beskrivning:
MST 15		305 mm (LxBxH: 620 x 400 x 2,8 mm).		
MST 55		160 mm för 625 mm undertak.		
MST 27		175 mm (för undertak 1200 mm).		
MST 28		250 mm (för undertak 1200 mm).		
MST 37		190 - 205 - 225 mm (för undertak 1200 mm).		
MST 38		130 - 155 - 170 mm (för undertak 1200 mm).		
MST 39		200 - 222 - 254 mm (för undertak 1200 mm).		
MST 42		200 mm (för undertak 1200 mm).		
MST 44		349 x 170 mm (för undertak 1200 mm).		
MST 57		162 x 355 mm (för 1200 mm undertak).		
MST 89		155 mm (för undertak 1200mm).		
MST 95		225 (för undertak 1200 mm).		
MST 109		215 (för undertak 1200 mm).		
MST 177		180 mm x 2 (240 mm CC). För undertak 1200 mm.		
MST 33		Vinkelplåtar för 600 mm undertak, par.		
MST 54		Vinkelplåtar för 1200 mm undertak, par.		
MST 13		222 mm. (LxBxH: 595 x 450 x 2,8 mm).		
MST 25		180 mm Twist.		
MST 29		375 mm (LxBxH: 595 x 450 x 2,8 mm).		
MST 40		345 mm (LxBxH: 595 x 450 x 2,8 mm).		
MST 46		320 mm (LxBxH: 595 x 450 x 2,8 mm).		
MST 138		360 mm (LxBxH: 595 x 400 x 2,8 mm).		
MST 355		355 mm (LxBxH: 595 x 510 x 2,8 mm).		
MST 381		380 mm (LxBxH: 595 x 580 x 2,8 mm).		
MST 31		Big Box 580 x 340 x 230 mm.		
MST 10	16 050 98	Hål/Markering 40 - 270 mm.		
MST 36		Bokad.		
MST 81		235 mm. (för undertak 900 mm).		